



**Accord®**

48" x 36" Vikrell® bath/shower wall set with Aging in Place grab bars  
72284103-V



**Features**

- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Geometric back wall design with convenient shelves for ample storage
- Easy-to-clean, durable high-gloss finish
- Includes three Aging in Place Matte Silver grab bars (one 80012222 and two 80001024)

**Material**

- Compression molded from our exclusive solid Vikrell® material

**Installation**

- Alcove
- Caulk-free installation

**Recommended Products/Accessories**

- 1500D-48 Framed pivot shower door
- 5475-48 Frameless sliding shower door
- 5970-48 Framed sliding shower door
- 5975-48 Framed sliding shower door
- 5976-48 Framed sliding shower door
- 547808-48 Frameless sliding shower door
- 581075-48 Frameless sliding shower door
- 72286104 Removable bath seat for Series 7228 and 7229
- K-23723 Faucet cleaner
- K-23733 Vikrell® cleaner

**Included Components**

- 80012222 22" curved grab bar
- 80001024 24" straight grab bar (Qty 2)



This product has been discontinued.

This product has been discontinued.


**Codes/Standards**

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- IAPMO Certification

**STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty**  
**STERLING® Grab Bars Ten-Year Limited Warranty**

See website for detailed warranty information.

**DISCONTINUED** This product has been discontinued.



**Technical Information**

All product dimensions are nominal.

Drain location: Center

Maximum door height: 70-5/8" (1794 mm)

Maximum door width: 44-5/8" (1133 mm)

Maximum door height: 70-5/8" (1794 mm)

Maximum door width: 44-5/8" (1133 mm)

**Notes**

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.