



**Accord®**

60" seated shower base  
**72291100**



### Features

- 3-1/2" threshold.
- Durable high-gloss finish with a molded-in textured floor.
- Center drain.
- Not suitable for tile-down application.
- Compatible with Accord complete wall set (series 7229)

### Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty.

### Recommended Products/Accessories

- 5475-59 Frameless sliding shower door
- 5477-59 Frameless sliding shower door
- 5970-59 Framed sliding shower door
- 5975-59 Framed sliding shower door
- 5976-59 Framed sliding shower door
- 5977-59 Framed sliding shower door
- 547808-59 Frameless sliding shower door
- 572075-59 Framed sliding shower door
- 581075-59 Frameless sliding shower door
- 80001012 12" straight grab bar
- 80001018 18" straight grab bar
- 80001024 24" straight grab bar
- 80011032 32" straight grab bar
- 80001036 36" straight grab bar
- 80012134 34" curved grab bar
- 72286104 Removable bath seat for Series 7228 and 7229
- K-23726 Drain treatment
- K-23733 Vikrell® cleaner



### Codes/Standards



None Applicable

### Warranty – Bathing Fixtures (and) Kitchen and Utility Sinks Made of Solid Vikrell® Material

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	0	White
	96	KOHLER Biscuit

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.sterlingplumbing.com](http://www.sterlingplumbing.com).

3-20-2020 08:51 - US



**Accord®**  
60" seated shower base  
**72291100**

No image available.  
This product is a component and not intended to be a standalone installation.

### **Technical Information**

All product dimensions are nominal.

Installation: Three-wall alcove

Drain location: Center

Maximum door width: 56-5/8" (1438 mm)

### **Notes**

Install this product according to the installation instructions.