



Medley®

48" x 34" Vikrell® shower with Aging in Place backerboards, center drain
72410106



Features

- 3-1/8" (79 mm) threshold
- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Smooth wall design with molded-in shelves and shaving ledges
- Easy-to-clean, durable high-gloss finish
- Factory-installed Aging in Place backerboards for future grab bar installation

Material

- Compression molded from our exclusive solid Vikrell® material

Installation

- Alcove
- Center drain
- Caulk-free installation

Recommended Products/Accessories

- 1500D-48 Framed pivot shower door
- 5475-48 Frameless sliding shower door
- 5970-48 Framed sliding shower door
- 5975-48 Framed sliding shower door
- 5976-48 Framed sliding shower door
- 547808-48 Frameless sliding shower door
- 581075-48 Frameless sliding shower door
- 80001012 12" straight grab bar
- 80001018 18" straight grab bar
- 80001036 36" straight grab bar
- 72186104 Freestanding bath seat
- K-23726 Drain treatment
- K-23733 Vikrell® cleaner

Included Components

- 72321100 48" x 34" Vikrell® shower base, center drain
- 72412106 48" Vikrell® shower back wall with Aging in Place backerboards
- 72405106 34" Vikrell® shower end wall set with Aging in Place backerboards



Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- HUD, UM Bulletin 73
- IAPMO Certification

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description



Color	Code	Description
	0	White

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.


For the most current Specification Sheet, go to www.sterlingplumbing.com.

3-26-2024 19:40 - US



End Wall

Back Wall



Note: Right and left end walls are the same, only mirrored.

□ □ Backer board locations

Technical Information

All product dimensions are nominal.

Drain location:	Center
Weight:	120 lbs (54.4 kg)
Minimum flat for door:	2-7/16" (62 mm)
Maximum door height:	70-3/4" (1797 mm)
Maximum door width:	45-5/8" (1159 mm)

Notes

Install this product according to the installation instructions.

Studs should be positioned roughly as shown. Double studding is recommended for pivot shower door installations.

Attach grab bars at the specified backer board locations only.