



Traverse®

60" x 34" x 75" Vikrell® shower with Aging in Place backerboards, center drain
72530106



Features

- Tongue-and-groove modular design allows for easy installation during any phase of construction
- Modern subway tile design
- Full-length shelf provides generous storage
- Easy-to-clean, durable high-gloss finish
- Factory-installed Aging in Place backerboards for future grab bar installation

Material

- Compression molded from our exclusive solid Vikrell® material

Installation

- Pro4™ installation system features a two-piece back wall design, enabling one-person handling and installation
- Alcove
- Center drain
- Caulk-free installation

Recommended Products/Accessories

- 80001012 12" straight grab bar
- 80001018 18" straight grab bar
- 80001024 24" straight grab bar
- K-23733 Vikrell® cleaner
- 581075-59 Frameless sliding shower door
- 547808-59 Frameless sliding shower door
- 5475-59 Frameless sliding shower door
- 5970-59 Framed sliding shower door
- 5976-59 Framed sliding shower door
- 5960-59 Framed sliding shower door
- 5960-57 Framed sliding shower door

Included Components

- 72331100 60" x 34" Vikrell® shower base, center drain
- 72532100 60" x 72-1/4" Vikrell® shower back wall
- 72505106 34" x 72-1/4" Vikrell® shower end wall set with Aging in Place backerboards
- 72321100 48" x 34" Vikrell® shower base, center drain
- 72522100 48" x 72-1/4" Vikrell® shower back wall
- 72505100 34" x 72-1/4" Vikrell® shower end wall set



Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- HUD, UM Bulletin 73
- IAPMO Certification

STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

	0	White
---	---	-------



Note: Right and left end walls are the same, only mirrored.

Technical Information

All product dimensions are nominal.

Drain location:	Center
Weight:	139 lbs (63 kg)
Minimum flat for door:	2-7/16" (62 mm)
Maximum door height:	72" (1829 mm)
Maximum door width:	56-9/16" (1437 mm)

Notes

Install this product according to the installation instructions.