



### Features

- 16" apron, 11" soaking depth
- Gently sloping backrest, six color-matched hydromassage jets with adjustable flow control

### Material

- Made from solid Vikrell® material for strength, durability, and lasting beauty

### Installation

- Alcove
- Right drain

### Recommended Products/Accessories

- 5425-59 Frameless sliding bath door
- 542808-59 55-1/2" H frameless sliding bath door with 5/16"-thick glass



**DISCONTINUED**

**ADA**

This product has been discontinued.


### Codes/Standards

- ASME A112.19.7/CSA B45.10
- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662
- UL 1795
- ADA
- ICC/ANSI A117.1
- IAPMO Certification
- UL Listed

**DISCONTINUED**

### STERLING® Vikrell® or Acrylic Baths and Shower Bases Ten-Year Limited Warranty

See website for detailed warranty information.



**Required Electrical Service**

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Pump: 120 V, 15 A, 60 Hz

**Technical Information**

All product dimensions are nominal.

- Drain location: Right
- Basin area, bottom: 40" x 21" (1016 mm x 533 mm)
- Basin area, top: 52" x 29" (1321 mm x 737 mm)
- Water depth: 11" (279 mm)
- Water capacity: 40 gal (151.4 L)
- Electrical component Pump: 120 V, 7 A, 60 Hz rating:
- Pump speed: Single
- Minimum flat for door: 3-1/4" (83 mm)

**Notes**

Install this product according to the installation instructions.

Provide one grounded electrical outlet within 24" (610 mm) of each component.

Measure your actual product for roughing-in details.

Pump is supplied with 24" (610 mm) grounding-type plug-in cord.

Locate the outlet behind the whirlpool, and within 24" (610 mm) of the pump.

Do not disassemble the pump or piping as this could void the warranty.

Size the drain cutout to fit the drain assembly that will be used.

Studs should be positioned roughly as shown.

ADA compliant when installed to the specific requirements of these regulations.