



Sunfield™

23" round lighted mirror
78900-23

Features

- Mirror with embedded LED lighting elevates your bathroom experience
- Color rendering true to a daylight experience achieved through >90 CRI (color rendering index)
- Tested at 4000 Kelvin and 1360 lumens for a favorable light experience
- Optimal lighting with energy efficiency at >45 lumens/watt
- Compatible with wall-mount LED dimmers (not included), which allow you to control lighting from multiple locations in the space
- LED life expectancy >50,000 hours
- Ideal for a 24"–36" vanity, pedestal sink or small space solution
- Two mirrors can be paired with a 60" double-basin vanity

Installation

- French cleat mounting system for quick, secure installation
- Power cord plug-in for easy electrical connection
- Includes mounting hardware

Recommended Products/Accessories

K-23723 Faucet cleaner




Codes/Standards

UL 962
CA Title 24 JA8
cUL Listed
UL Listed

STERLING® One-Year Limited Warranty

See website for detailed warranty information.



Required Electrical Service

One circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Lights: 120 V, 0.5 A, 60 Hz

Technical Information

All product dimensions are nominal.

Mirror type: Wall-mount

Lighting included: Yes

Electrical component rating: Lights: 1.04 A, 60 Hz, 25 W, 1360 Lumens, 4000K

Notes

Install this product according to the installation instructions.

Connect this product only to a properly grounded outlet.

If there is not a wall stud to attach the mirror to, use anchors provided.