



Sunfield™

37" x 24" lighted mirror
78901-37

Features

- Mirror with embedded LED lighting elevates your bathroom experience.
- Color rendering true to a daylight experience achieved through >90 CRI (color rendering index).
- Tested at 4000 Kelvin and 2500 lumens for a favorable light experience.
- Optimal lighting with energy efficiency at >58 lumens/watt.
- Compatible with wall-mount LED dimmers (not included), which allow you to control lighting from multiple locations in the space.
- LED life expectancy >50,000 hours.
- Pairs well with a 30"–36" vanity when mounted vertically 37"H x 24"W.
- Pairs well with a 42"–48" vanity when mounted horizontally 24"H x 37"W.

Material

- Anodized aluminum back frame and installation bracket.

Installation

- French cleat mounting system for quick, secure installation.
- Power cord plug-in for easy electrical connection.
- Includes mounting hardware.


Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:

Mounting hardware




Codes/Standards

UL 962
CA Title 24 JA8

STERLING® One-Year Limited Warranty

See website for detailed warranty information.



Required Electrical Service

One circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Lights: 120 V, 0.9 A, 60 Hz

Technical Information

All product dimensions are nominal.

Mirror type: Wall-mount

Lighting included: Yes

Electrical component rating: Lights: 1.96 A, 60 Hz, 47 W

Notes

Install this product according to the installation instructions.

Connect this product only to a properly grounded outlet.

If there is not a wall stud to attach the mirror to, use anchors provided.