



McAllister®
Under-Mount Kitchen Sink
96029

Features

- 9-deep double bowls.
- 3-3/4" drain opening.
- Stainless steel with luster finish.
- SilentShield® sound-absorption technology offers quieter performance.

Material

- Premium 18-gauge stainless steel.

Installation

- Undermount.
- No faucet holes; requires wall-or counter-mount faucet.

Recommended Products/Accessories

- 11862 Sink Rack
- 11863 Sink Rack
- 7400 Sink Strainer
- K-6139 Sponge Caddy
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner




Codes/Standards

ASME A112.19.3/CSA B45.4

STERLING® Warranty - Stainless Steel Sinks

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

- Installation: Under-mount
- Bowl area (Left): Length: 14-3/16" (360 mm)
Width: 18-7/16" (468 mm)
Bowl depth: 8-11/16" (221 mm)
Water depth: 8-11/16" (221 mm)
- Bowl area (Right): Length: 14-3/16" (360 mm)
Width: 15-11/16" (398 mm)
Bowl depth: 8-11/16" (221 mm)
Water depth: 8-11/16" (221 mm)
- Drain hole: 3-5/8" (92 mm)
- Template: 1315847-7, required, included

Notes

- Install this product according to the installation instructions.
- Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1-800-43-FOCUS). Kohler Co. is not responsible for cut-out errors when the incorrect cut-out template is used.