

# McAllister®

**Under-Mount Kitchen Sink** 97447

#### **Features**

- 8"-deep single bowl.
- 3-3/4" drain opening.
- Stainless steel with luster finish.
- SilentShield® sound-absorption technology offers quieter performance.

#### Material

Premium 18-gauge stainless steel.

#### Installation

- Undermount.
- No faucet holes; requires wall-or counter-mount faucet.

#### **Recommended Products/Accessories**

K-23726 Drain treatment K-23729 Stainless steel cleaner

#### **Included Components**

Additional Components: Mounting hardware



#### Codes/Standards

ASME A112.19.3/CSA B45.4 All applicable US Federal and State material regulations


### STERLING® Warranty - Stainless Steel

See website for detailed warranty information.



#### **McAllister®**

## Under-Mount Kitchen Sink 97447



#### **Technical Information**

All product dimensions are nominal.

Bowl configuration: Single

Installation: Under-mount

Bowl area: Length: 21" (533 mm)

Width: 15-1/4" (387 mm) Bowl depth: 7-3/4" (197 mm)

Water depth: 7-3/4" (197 mm)

Drain hole: 3-5/8" (92 mm)

Template: 1315840-7, required, included

#### **Notes**

Install this product according to the installation instructions.