



McAllister®
Undermount single-bowl kitchen sink
97447

Features

- No faucet holes; requires wall- or counter-mount faucet.
- 8" (203 mm) depth.
- 3-3/4" drain opening.
- Stainless steel with luster finish.

Material

- Premium 18-gauge stainless steel.

Installation

- Undermount.

Recommended Products/Accessories

- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Included Components

- Additional Components:
- Mounting hardware




Codes/Standards

- ASME A112.19.3/CSA B45.4
- All applicable US Federal and State material regulations

STERLING® Warranty - Stainless Steel Sinks

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

- Bowl configuration: Single
- Installation: Under-mount
- Bowl area: Length: 21" (533 mm)
Width: 15-1/4" (387 mm)
Bowl depth: 7-3/4" (197 mm)
Water depth: 7-3/4" (197 mm)
- Drain hole: 3-5/8" (92 mm)
- Template: 1315840-7, required, included

Notes

Install this product according to the installation instructions.