



Features

- One hole predrilled and two additional locations marked on the sink to create additional holes if needed
- 12-1/4" depth
- Unique quarter-deck design provides shelf space for storage and cleaning
- Surface texture maintains superior stain- and scratch-resistance
- Includes a freestanding metal stand for added storage and versatility
- 36" (914 mm) comfortable working height
- Sink drain with strainer sold separately

Material

- Compression molded from our exclusive solid Vikrell® material

Recommended Products/Accessories

7400 Stainless Steel Sink Drain and Strainer
K-23726 Drain treatment
K-23733 Vikrell® cleaner



Codes/Standards

CSA B45.5/IAPMO Z124
ASTM E162
ASTM E662
IAPMO Certification


STERLING® Vikrell® or Acrylic Kitchen and Utility Sinks Lifetime Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	0	White
-------------------------------------------------------------------------------------	---	-------



Technical Information

All product dimensions are nominal.

- Bowl configuration: Single
- Bowl area (Only): Length: 22" (559 mm)
Width: 16" (406 mm)
Bowl depth: 12-1/4" (311 mm)
Water depth: 12-1/4" (311 mm)
- Number of deck holes: 3
- Faucet hole(s): 1-3/8" (35 mm)
- Drain hole: 3-1/2" (89 mm)

Notes

Install this product according to the installation instructions.