



15" top-mount single-bowl bar sink
B155B-2

Features

- Two faucet holes
- 5-1/2" (140 mm) depth
- 2" drain opening
- Stainless steel with luster bowl finish and a satin deck finish

Material

- Premium 22-gauge stainless steel

Installation

- Top-mount

Recommended Products/Accessories

K-23726 Drain treatment

K-23729 Stainless steel cleaner

Optional Products/Accessories

7400 Stainless Steel Sink Drain and Strainer



ADA

Codes/Standards

ASME A112.19.3/CSA B45.4

ADA

ICC/ANSI A117.1

IAPMO Certification

**STERLING® Stainless Steel Sinks
Lifetime Limited Warranty**





See website for detailed warranty information.

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

3-25-2024 21:52 - US



Technical Information

All product dimensions are nominal.

- Center(s): 4
- Bowl area (Only): Length: 13-1/4" (337 mm)
Width: 11" (279 mm)
Bowl depth: 5-9/16" (141 mm)
Water depth: 5-9/16" (141 mm)
- Number of deck holes: 2
- Faucet hole spacing: 4" (102 mm)
- Faucet hole(s): 1-7/16" (37 mm)
- Drain hole: 1-15/16" (49 mm)

Notes

Install this product according to the installation instructions.
ADA compliant when installed to the specific requirements of these regulations.