



# Economy

## Neo-angle corner shower kit

### NI3190A-38

#### Features

- No track-cutting required.
- Convenient corner shelves for shower essentials.
- Polypropylene shower base.
- Thermoformed styrene wall surround.
- Tempered glass ensures maximum safety and durability.

#### Installation

- Door can be installed to open to the left or right to suit your bathroom layout.
- Not for use in hospitality.
- For residential use only.

#### Included Components

Product consists of:

- I3838N-W Neo-angle shower base
- K2510-SW Neo-angle shower wall surround
- 7360000 Shower Drain



#### Codes/Standards

- ANSI Z97.1
- CPSC 16CFR 1201

#### STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

#### Available Glass Options

Code	Description
------	-------------

	Hammered
--	----------


---

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.sterlingplumbing.com](http://www.sterlingplumbing.com).

3-10-2020 06:34 - US



### Technical Information

All product dimensions are nominal.

Installation type: For shower base installation

Walk-through - Min:  $22''$  (559 mm)

Walk-through - Max:  $22''$  (559 mm)

Base-To-Wall Radius  $3/8''$  (10 mm)

- Max:

### Notes

Measure your actual product for roughing-in details.

The vertical opening should be a minimum of  $72''$  (1829 mm) to allow for installation clearance.