



Intrigue™

Framed neo-angle corner shower door

SP2270A-38

Features

- Framed, 1/8" (3 mm) thick tempered glass.
- Full-length handle.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.

Technology

- Fits STERLING® Intrigue™ neo-angle shower, Series 7204, only.

Installation

- Door can be installed to open to the left or right to suit your bathroom layout.
- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

- 72041100 39" neo-angle shower base
- 72040100 39" tile neo-angle shower
- K-23723 Faucet cleaner

Included Components

- Additional Components:
Hardware kit



Codes/Standards

- ANSI Z97.1
- CPSC 16CFR 1201


STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.


Color	Code	Description
-------	------	-------------

	S	Silver
--	---	--------

Available Glass Options




Code	Description
------	-------------

	Pebbled
--	---------



Note: Dimensions are taken on centerline of curb/threshold at the rough opening.

* Walk-through



Technical Information

All product dimensions are nominal.
 Installation type: For shower base installation
 Walk-through - Min: 23" (584 mm)
 Walk-through - Max: 27-9/16" (700 mm)
 Base-To-Wall Radius 3/8" (10 mm)
 - Max:
 Glass thickness: 1/8" (3 mm)

Notes

Install this product according to the installation guide.
 The vertical opening should be a minimum of 75-1/2" (1918 mm) to allow for installation clearance.