



# Intrigue™

Framed neo-angle corner shower door

## SP2270A-38

### Features

- Framed, 1/8" (3 mm) thick tempered glass
- Full-length handle
- Tempered glass ensures enhanced safety and durability
- Fits STERLING® Intrigue™ neo-angle shower, Series 7204, only

### Material

- Anodized aluminum prevents rust and corrosion

### Installation

- Out-of-plumb adjustability simplifies installation
- Door can be installed to open to the left or right to suit your bathroom layout
- Not for use in hospitality
- For residential use only

### Recommended Products/Accessories

72041100 39" x 39" Vikrell® neo-angle shower base, center drain



### Codes/Standards


ANSI Z97.1  
CAN/CGSB-12.1  
CPSC 16CFR 1201

### STERLING® Bath and Shower Doors Five-Year Limited Warranty

See website for detailed warranty information.




### Available Glass Options

Code	Description
	Pebbled



Note: Dimensions are taken on centerline of curb/threshold at the rough opening.

\* Walk-through



### Technical Information

All product dimensions are nominal.

Base-To-Wall 3/8" (10 mm)

Radius – Max:

### Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 75-1/2" (1918 mm) to allow for installation clearance.