



# Intrigue™

## Framed neo-angle corner shower door

### SP2277A-38

#### Features

- Frameless.
- Framed, 1/8" (3 mm) thick tempered glass.
- Full-length handle.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.

#### Technology

- Fits STERLING® Intrigue™ neo-angle shower, Series 7204, only.

#### Installation

- Door can be installed to open to the left or right to suit your bathroom layout.
- Not for use in hospitality.
- For residential use only.

#### Recommended Products/Accessories

72041100 39" neo-angle shower base  
72040100 39" tile neo-angle shower  
K-23723 Faucet cleaner

#### Included Components

Additional Components:  
Hardware kit



#### Codes/Standards

ANSI Z97.1  
CPSC 16CFR 1201


#### STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

#### Available Colors/Finishes

*Color tiles intended for reference only.*


Color	Code	Description
-------	------	-------------

	S	Silver
--	---	--------

#### Available Glass Options




Code	Description
------	-------------

	Ellipse
--	---------



Note: Dimensions are taken on centerline of curb/threshold at the rough opening.

\* Walk-through



**Technical Information**

All product dimensions are nominal.  
 Installation type: For shower base installation  
 Walk-through - Min: 23" (584 mm)  
 Walk-through - Max: 27-9/16" (700 mm)  
 Base-To-Wall Radius 3/8" (10 mm)  
 - Max:  
 Glass thickness: 1/8" (3 mm)

**Notes**

Install this product according to the installation guide.  
 The vertical opening should be a minimum of 75-1/2" (1918 mm) to allow for installation clearance.