



Intrigue™

Framed neo-angle corner shower door

SP2277A-38

Features

- Frameless
- Framed, 1/8" (3 mm) thick tempered glass
- Full-length handle
- Tempered glass ensures enhanced safety and durability
- Fits STERLING® Intrigue™ neo-angle shower, Series 7204, only

Material

- Anodized aluminum prevents rust and corrosion

Installation

- Out-of-plumb adjustability simplifies installation
- Door can be installed to open to the left or right to suit your bathroom layout
- Not for use in hospitality
- For residential use only

Recommended Products/Accessories

72041100 39" x 39" Vikrell® neo-angle shower base, center drain



Codes/Standards


ANSI Z97.1
CAN/CGSB-12.1
CPSC 16CFR 1201

STERLING® Bath and Shower Doors Five-Year Limited Warranty

See website for detailed warranty information.




Available Glass Options

Code	Description
	Ellipse



Note: Dimensions are taken on centerline of curb/threshold at the rough opening.

* Walk-through



Technical Information

All product dimensions are nominal.

Base-To-Wall 3/8" (10 mm)

Radius – Max:

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 75-1/2" (1918 mm) to allow for installation clearance.