

Features

- Frameless.
- 1/4" (6 mm) thick tempered glass.
- CleanCoat® nanotechnology provides a smooth, nonstick surface to help prevent buildup of water stains, bacteria and mildew on your glass, to make it easy to clean and keep it looking like new.
- Knob handle.

Technology

- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.
- Fits STERLING® Intrigue™ neo-angle shower, Series 7204, only.

Installation

- Door can be installed to open to the left or right to suit your bathroom layout.
- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

- 72041100 39" x 39" neo-angle shower base
- 72040100 39" x 39" x 79" tile neo-angle shower stall
- K-23723 Faucet cleaner

Included Components

- Additional Components:
Hardware kit



Codes/Standards

- ANSI Z97.1
- CPSC 16CFR 1201

STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.


Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	DR	Deep Bronze
	N	Nickel
	S	Silver

Available Glass Options

Code	Description
	Clear
	Frosted



Technical Information

All product dimensions are nominal.

Installation type: For shower base installation

Walk-through - Min: 23-7/8" (606 mm)

Walk-through - Max: 29-7/16" (748 mm)

Base-To-Wall Radius 3/8" (10 mm)

- Max:

Glass thickness: 1/4" (6 mm)

Glass coating: CleanCoat®

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 74-1/4" (1886 mm) to allow for installation clearance.