



A KOHLER COMPANY

Finesse™

Frameless sliding shower door SP5465-45

Features

- Frameless.
- 1/4" (6 mm) thick tempered glass.
- CleanCoat® nanotechnology provides a smooth, nonstick surface to help prevent buildup of water stains, bacteria and mildew on your glass, to make it easy to clean and keep it looking like new.

Technology

- Inside and outside towel bars complete the look of this door.
- Out-of-plumb adjustability.
- Tempered glass ensures maximum safety and durability.
- Anodized aluminum prevents rusting and corrosion.
- Fits the STERLING® Advantage™ 48" shower only, Series 6203.

Installation

- Not for use in hospitality.
- For residential use only.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:
Hardware kit



Codes/Standards

ANSI Z97.1
CPSC 16CFR 1201

STERLING® Warranty - Bath and Shower Doors

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	DR	Deep Bronze
	N	Nickel
	S	Silver

Available Glass Options


Code	Description
	Clear

1-800-STERLING (1-800-783-7546)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.sterlingplumbing.com.

8-23-2020 08:46 - US/CA



Technical Information

All product dimensions are nominal.

Installation type: For shower base installation

Opening Width - Min: $39\text{-}\frac{11}{16}\text{''}$ (1008 mm)

Opening Width - Max: $44\text{-}\frac{11}{16}\text{''}$ (1135 mm)

Walk-through - Min: $13\text{-}\frac{7}{8}\text{''}$ (352 mm)

Walk-through - Max: $18\text{-}\frac{7}{8}\text{''}$ (479 mm)

Base-To-Wall Radius $\frac{1}{2}\text{''}$ (13 mm)

– Max:

Glass thickness: $\frac{1}{4}\text{''}$ (6 mm)

Glass coating: CleanCoat®

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of $67\text{-}\frac{1}{4}\text{''}$ (1708 mm) to allow for installation clearance.