

Features

- 5", 7"-deep double bowls.
- 3-3/4" drain opening.
- Stainless steel with luster finish.
- SilentShield[®] sound-absorption technology offers quieter performance.

Installation

- Undermount.
- No faucet holes; requires wall-or counter-mount faucet.

Recommended Products/Accessories

7400 Sink Strainer K-6139 Sponge Caddy K-23726 Drain treatment K-23729 Stainless steel cleaner

Included Components

Product consists of: 91915 Hardware Kit



McAllister®

UCL3322R


Under-Mount Kitchen Sink


Codes/Standards ASME A112.19.3/CSA B45.4

STERLING[®] Warranty - Stainless Steel Sinks See website for detailed warranty information.



McAllister® Under-Mount Kitchen Sink UCL3322R





Technical Information

All product dimensions are nominal.	
Bowl configuration:	High-low
Installation:	Under-mount
Bowl area (Left):	Length: 7-1/4" (184 mm)
	Width: 15-1/4" (387 mm)
	Bowl depth: 5" (127 mm)
	Water depth: 5" (127 mm)
Bowl area (Right):	Length: 21" (533 mm)
	Width: 15-1/4" (387 mm)
	Bowl depth: 7" (178 mm)
	Water depth: 7" (178 mm)
Drain hole:	3-5/8" (92 mm)
Template:	1154796-7, required, included

Notes

Install this product according to the installation instructions.

Measure your actual product for roughing-in details.