



McAllister®
32-3/4" undermount double-bowl kitchen sink
UCL3322R

Features

- No faucet holes; requires wall- or counter-mount faucet
- 5" depth left bowl, 7" depth right bowl
- 3-3/4" (94 mm) drain opening
- Stainless steel with luster finish

Material

- Premium 19-gauge stainless steel

Installation

- Undermount

Recommended Products/Accessories

- 7400 Stainless Steel Sink Drain and Strainer
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Included Components

- 91915 Hardware Kit





Codes/Standards

- ASME A112.19.3/CSA B45.4
- IAPMO Certification

STERLING® Stainless Steel Sinks

Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

- Bowl configuration: High-low
- Bowl area (Left): Length: 7-1/4" (184 mm)
Width: 15-1/4" (387 mm)
Bowl depth: 5" (127 mm)
Water depth: 5" (127 mm)
- Bowl area (Right): Length: 21" (533 mm)
Width: 15-1/4" (387 mm)
Bowl depth: 7" (178 mm)
Water depth: 7" (178 mm)
- Drain hole: 3-5/8" (92 mm)
- Template: 1154796-7, required, included

Notes

- Install this product according to the installation instructions.
- Measure your actual product for roughing-in details.