
KOHLER_® AEGIS_®

EFI 27–30 HP Engines



LESS WEAR AND TEAR ON YOUR MACHINE. AND YOUR WALLET.

Your utility vehicle or heavy-duty construction equipment has some big jobs ahead. You need an engine that can stand up to the task. Again and again. That's why we built the Aegis® EFI 27–30 hp engine. Its liquid-cooled designed means less wear and tear, fewer repairs and more power in a smaller frame. It's the engine that can stand up to anything you throw at it.



BUILT TO LAST

 Liquid-cooled to provide better engine durability

MORE RELIABLE


- No carburetor—no carburetor problems
- Electronic fuel injection automatically optimizes for fuel quality


EASY MAINTENANCE


 Proprietary EFI diagnostic software provides quick and easy troubleshooting to minimize downtime

KOHLER_® AEGIS_®


EFI 27–30 HP Engines








Starter side view





MAXIMUM POWER



2000 2200 2400 2600 2800 3000 3200 3400 3600 REVOLUTIONS PER MINUTE

FEATURES AND OPTIONS







ENGINE TYPE		Four-cycle, single-cylinder, overhead valve, cast-iron cylinder liners, liquid-cooled, gasoline, horizontal shaft, hydraulic valve lifters		
MODEL		ELH750	ELH775	
GROSS POWER @ 3600 RPM	Max. hp (kW)	27 (20.1)	30 (22.4)	
DISPLACEMENT	cu in (cc)	46 (747)		
BORE	in (mm)	3.3 (83)		
STROKE	in (mm)	2.7 (69.0)		
PEAK TORQUE @ RPM	ft-lb (Nm)	42.9 (58.2) @ 2400	44.6 (60.5) @ 3400	
COMPRESSION RATIO		8.7:1		
DRY WEIGHT	lb (kg)	116 (53)		
OIL CAPACITY	U.S. qt (L)	2.0 (1.9)		
LUBRICATION		Full-pressure lubrication with full-flow filter		
DIMENSIONS* L x W x H	in (mm)	17 x 18.1 x 26.5 (432 x 460 x 675)		

^{*}Length is radiator to closure plate. Width is radiator from side to side. Height is mounting feet to rain cap.

STANDARD FEATURES

Liquid-cooled with	Closed-loop electronic	PTO side-load	Solenoid fuel shutdown
high-efficiency radiator	fuel injection	sleeve bearing	
			Oil Sentry _™ automatic
Overhead valve design	25-amp charging, regulated	Hydraulic valve lifters	low-oil shutdown system (installed,
Cast-iron cylinder liners		12-volt solenoid shift	not wired)
	Yellow oil cap	electric start	
Dedicated engine	and dipstick		Full-pressure
ground		Dual-element	lubrication/full-flow filter
	Large filters	air cleaner	
Debris screen	(air, oil, fuel)		3-year commercial
		Dual oil drains	limited warranty
Engine-mounted	Hardened crank		
high-pressure fuel pump	journals	Electronic ignition	

POPULAR FACTORY OPTIONS

Remote oil filter	5% governor	Chopper-type grass screen	60-amp charging, regulated and fused	
Variety of mufflers	SAE A/B pump mounts	Additional crank sizes	Minimum of 20 amps	
Exhaust deflector/spark arrestor	Choice of air cleaners (flat, HD, WAWB)	Flywheel PTOs	at 1000 RPM	
Engine-mounted controls (CH)	Guard for rotating grass screen	Oil cooler		



For more information, contact your KOHLER source of supply.
Or call toll-free in the U.S. and Canada 800-544-2444.