

KOHLER. COMMAND PRO. 7.75 to 11 Ft-Lbs Engines



IMAGINE THE ULTIMATE COMMERCIAL ENGINE. NOW OPEN YOUR EYES.

When your crew's out for a job, they need power they can count on—no matter the conditions. Enter KOHLER_® Command PRO_® 173 to 224-cc walk-behind engines. The ultimate in durability with bestin-class power* to cover more ground quicker than ever before.



KOHLER COMMAND PRO ENGINES CV224, CV200, CV173

BUILT TO LAST

- Full-pressure lubrication with Clean-Change™ oil filter for easy, no-mess oil changes
- Fully sealed, four-stage cyclonic Quad-Clean™ air filter protects engine from dirt and debris
- Die-cast valve covers with reusable rubber gasket
- Steel oil pump gear
- Stamped-steel engine cover and recoil assembly

POWER. PRODUCTIVITY. PROFIT.

- Best-in-class power*
- Industry-leading torque with engine models at 11.0, 9.50 or 7.75 ft-lb—to make short work of tall grass
- KOHLER_☉ Consistent-Cut_™ technology for higher engine speed in tough grass for a cleaner turf cut

WE'VE GOT YOUR BACK


• Three-year limited commercial warranty


ALL OF THE PROTECTION, NONE OF THE MESS


 Clean-Change_™ Technology – allows for easy oil changes without the mess

KOHLER_® **COMMAND PRO**_® 7.75 to 11 Ft-Lbs Vertical-Shaft Engines

HEAVY-DUTY AIR CLEANER











Top view



Isometric view







KOHLER. COMMAND PRO.





CV224

ENGINE TYPE		Four-cycle, gasoline, OHV, cast-iron cylinder liners, aluminum block		
MODEL		CV173	CV200	CV224
GROSS POWER @ 2600 RPM	ft-lb (Nm)	7.75 (10.5)	9.50 (12.9)	11.0 (14.9)
DISPLACEMENT	cu in (cc)	10.6 (173)	12.2 (200)	13.7 (224)
BORE	in (mm)	2.8 (70)	2.9 (73)	2.9 (73)
STROKE	in (mm)	1.8 (45)	1.9 (48)	2.1 (53.5)
COMPRESSION RATIO		8.0:1	8.9:1	9.2:1
DRY WEIGHT	lb (kg)	36.2 (16.4)	37.0	(16.8)
OIL CAPACITY	U.S. qt (L)	0.63 (0.6)		
LUBRICATION		Dual-Pressure lubrication with full-flow filter and splash		
DIMENSIONS* L x W x H	in (mm)	15.7 x 13.9 x 11.1 (399 x 353 x 281)		

*Length is front of valve cover to back of blower housing. Width is side to side. Height is mounting surface to grass screen.

STANDARD FEATURES

Cast-iron cylinder bore	Stamped-steel engine cover	Engine-mo controls
Die-cast valve cover with reusable rubber gasket	Stamped-steel recoil assembly	Quad-Clea stage, cyc
Full-pressure lubrication with spin-on oil filter	Easy-Pull _™ starting	Die-cast ir
Steel oil pump	1.4I Accu-Fill _™ (easy-fill) fuel tank	Rear pull z
Clean-Change _™ oil pan	High-mount oil dipstick	Zone start 25 mm x 7 4.75 mm x

Konnand PRO mnand PRO 3 Year Warranty 4 10 Million group corque 220.00

POPULAR FACTORY OPTIONS

BBC-compatible crankshaft - 7/8" x 61.415 mm x 4.75 mm keyway, threaded OD Side pull (3 o'clock) recoil assembly





ne-mounted rols	In-line fuel filter
d-Clean _™ four	Front discharge muffler with guard
e, cyclonic air filter	EPA-compliant
cast intake manifold	CARB-compliant
pull zone start	EU Stage V-compliant
e start crankshaft– m x 79.175 mm x mm x 7/16-20	Three-year commercial warranty

Side discharge muffler

Variable speed 1800-3500 rpm



For more information, contact your KOHLER source of supply. Kohler Co. reserves the right to make modifications without prior notice.



 Frinted in Italy
 ED0035585810
 Rev.00 02/20 Eng
 KOHLER CO.