
KOHLER® SH SERIES

5.5–6.5 HP Engines





Tough as nails. The hard-working KOHLER_® SH Series_™ engine is designed for quick, easy maintenance. Heavy-duty features like a cast-iron cylinder liner give consumers the same engine protection the pros need. Larger displacement results in more power. Built to last, so you get more hours out of your equipment.

DURABLE & RELIABLE

BUILT FOR THE PRO.

- Better fuel efficiency and cleaner emissions with overhead valve design vs. L-head design
- · Built to last with heavy-duty crankshaft and cast-iron cylinder liner
- Added protection with Oil Sentry_™ automatic low-oil shutdown system

EASY TO USE

- · Effortless starts with large indexable recoil starter and dual ball bearings
- Smooth operation from reduced noise and vibration
- Stop less and work more with large fuel tank



EASY TO MAINTAIN


- Easy maintenance and less downtime with dual oil fills and drains
- Simple, easy-access controls and no-tools-required air cleaner

TOTAL SUPPORT


- We stand behind our dealers. And they stand behind our warranty
- Need a replacement part? It's in stock now, not later
- KOHLER genuine parts are built for the long haul to give you peace of mind


KOHLER® SH SERIES


5.5–6.5 HP Engines




Top view









FEATURES AND OPTIONS



KOHLER_® SH SERIES_™

ENGINE TYPE		Four-cycle, single-cylinder, slant-cylinder, OHV, air-cooled, gasoline, horizontal shaft, aluminum head and crankcase with cast-iron cylinder liner.	
MODEL		SH255	SH265
GROSS POWER @ 3600 RPM*	Maximum hp (kW)	5.5 (4.2)	6.5 (4.8)
DISPLACEMENT	cu in (cc)	12 (196)	
BORE	in (mm)	2.7 (68)	
STROKE	in (mm)	2.1 (54)	
PEAK TORQUE @ 3000 BPM	ft-lb (Nm)	10.0 (13.6) @ 3000	10.2 (13.8) @ 3000
COMPRESSION RATIO		8.5:1	
DRY WEIGHT (RECOIL START)	lb (kg)	35.3 (16)	
OIL CAPACITY	U.S. qt (L)	0.6 (.6)	
FUEL CAPACITY	U.S. qt (L)	3.4 (3.3)	
LUBRICATION		Splash	
DIMENSIONS† L x W x H	in (mm)	9.9 x 14.5 x 14.6 (253 x 369 x 371)	
CRANKSHAFT HEIGHT	in (mm)	4.2 (106)	

^{*}Horsepower ratings exceed Society of Automotive Engineers Small Engine Test Code J1940. Actual engine horsepower is lower and affected by, but not limited to, accessories (air cleaner, exhaust, charging, cooling, fuel pump, etc.), application, engine speed and ambient operating conditions (temperature, humidity and altitude). For more information, contact Kohler Co. Engine Engineering. Kohler reserves the right to change product specifications, designs and equipment without notice and without incurring obligation.

[†]Engine measurements based on a base engine without electric start. Length is recoil starter to PTO face.



STANDARD FEATURES

OHV slant cylinder Quiet muffler with Sound-deadening Silenced air intake heat shield alloy crankcase Cast-iron cylinder liner Indexable Easy-Pull™ CARB Tier 3-compliant Dual ball bearings recoil starter Large-capacity metal fuel tank Easy-access throttle, Carburetor bowl drain Remote throttle (built-in) choke and fuel shutoff In-neck fuel Dual oil fills and drains 2-year consumer debris screen Automatic compression limited warranty Dual-element release Water trap in carburetor air cleaner

POPULAR FACTORY OPTIONS

12-volt starter

Exhaust deflector

Electronic ignition

Spark arrestor

3- and 10-amp charging systems

Crankshaft/PTO variations (keyed, tapered, threaded)

Mechanical governor

Low-profile air cleaner and muffler (generator)

EU noise-compliant

High-inertia flywheel

 $\begin{array}{l} \text{Oil Sentry}_{^{\text{TM}}} \text{ automatic} \\ \text{low-oil shutdown} \\ \text{system} \end{array}$

EMC/RFI-compliant

Fuel Secure_™ auto fuel shutoff



For more information, contact your KOHLER source of supply.
Or call toll-free in the U.S. and Canada 800-544-2444.