



KOHLER
CONFIDANT® EFI 20-27 HP

KOHLER Engines

EFI TECHNOLOGY. NOW AVAILABLE FOR WEEKEND WARRIORS.

Ditch that inefficient engine and get the same reliable power and fuel savings that commercial landscapers enjoy. Confidant® EFI boasts closed-loop electronic fuel injection that gives the performance of a pro-grade engine in ZTRs.

SAVES TIME AND MONEY

Uses 25% less fuel* than a carbureted engine – so you skip one out of every four trips to the gas station.

STARTS LIKE YOUR CAR

Just turn the key and go. Automotive-grade fuel injection technology provides easy starts in any condition or after long periods of storage.

MORE RELIABLE

You don't have to worry about bad gas or fuel storage issues – KOHLER® electronic fuel injection automatically optimizes for fuel quality.

THE BRAND YOU CAN TRUST

From the first name in EFI, backed with a 3-year limited warranty.

*Compared to a comparable KOHLER carbureted engine.

Take a look. And see how much you'll save.

Price of gasoline per gallon	\$ 2.50	\$ 2.75	\$ 3.00	\$ 3.25	\$ 3.50	\$ 3.75	\$ 4.00	\$ 4.25	\$ 4.50	\$ 4.75	\$ 5.00
Dollars saved per hour	\$ 0.75	\$ 0.83	\$ 0.90	\$ 0.98	\$ 1.05	\$ 1.13	\$ 1.20	\$ 1.28	\$ 1.35	\$ 1.43	\$ 1.50

For more information, contact your KOHLER source of supply.
Or call toll-free in the U.S. and Canada 800-544-2444.

Kohler Co., Kohler, Wisconsin 53044 Tel 920-457-4441

KohlerEngines.com

© 2015 by Kohler Co. All rights reserved.

KOHLER Engines

Printed in U.S.A. E-2269 10/15