

# KOHLER® COMMAND PRO® EFI

824 cc Engines



**KOHLER®**  
IN POWER. SINCE 1920.

# Get more muscle. SAVE MORE FUEL.



Power or fuel savings—that was your choice. Until now. Say hello to the Command PRO® EFI 824. With best-in-class\* torque it's ready to take on any terrain. And with the massive amount you save on fuel, it's the best thing your bottom line has ever seen. Man, it's good to be king.

## BEST-IN-CLASS TORQUE\*

- Tackles any terrain and won't back down.
- KOHLER® electronic fuel injection system automatically optimizes for fuel quality, altitude and weather for consistent power wherever you go.

## HUGE FUEL SAVINGS

- EFI reduces fuel usage, extends run times\*\*
- Designed and tuned for higher performance using less fuel.

## MORE RELIABLE, HIGHER PRODUCTIVITY

- No carburetor—no carburetor problems, maintenance or replacement costs.
- Less refueling means less downtime.
- 3-year unlimited—hour limited commercial warranty.

## EASY STARTS

- Starts like your car—just turn the key and go.

\*Class defined as vertical-shaft, commercial 800cc to 875 cc gasoline engines.

\*\*Compared to a comparable KOHLER carbureted engine under comparable loads and duty cycles.

**KOHLER**  
IN POWER. SINCE 1920.

For more information, contact your KOHLER source of supply, or call toll-free in the U.S. and Canada 800-544-2444.

**KOHLERPOWER.COM**

PRINTED IN U.S.A. E-2231-B 5/17 © 2017 KOHLER CO.