







MODEL	ENCLOSURE WEIGHT KG [LBS]
STEEL WEATHER	340 [750]
STEEL SOUND	363 [800]
ALUMINUM SOUND	227 [500]

NOTE:
1. TANK (IF ORDERED) MOUNTS BELOW SKID
2. TANK MAY EXTEND BEYOND ENCLOSURE (DISCHARGE END ONLY)



6X Ø25.4 [1.0] STD MOUNTING HOLES
12X Ø25.4 [1.0] IBC MOUNTING HOLES


DIMENSIONS IN [] ARE INCH EQUIVALENTS
(*) DESIGNATES 125KW 4045HF ENGINE

125 MODEL 4S11, 4S13, 4R12X, 4R13X, 4T13X
150 MODEL 4S13, 4S15, 4R13X, 4T13X, 4S12X, 4S13X
RECONNECTABLE
IMPROVE MOTOR STARTING (IMS) RECONNECTABLE
600V & 1 PHASE ALTERNATORS
4045HF285 & 6068HF285 JOHN DEERE TIER III

REV	DATE	ON COMPOSITE DWGS. SEE PART NO. FOR REVISION LEVEL	BY	UNLESS OTHERWISE SPECIFIED - 1) DIMENSIONS ARE IN MILLIMETERS 2) TOLERANCES ARE:	125KW 4045HF ENGINE
B	7-29-10	(A-6) 6X 17.5 NOTE ADDED [90041]	SAM	X.XX ± 0.25 X.X ± 1.0 X ± 1.5	
C	9-28-10	(A-5) 12X Ø17.5 ADDED [90301]	SAM	ANGLES ± 0° 30'	
D	1-3-12	(A-4) 125 & 150 MODEL NOTE UPDATED [92681]	PKD		
E	2-5-12	(A-1) 1-2 WAS 1-1, SEE SHEET 2 [CT32174]	SAM		
F	10-3-13	(A-5) Ø25.4 [1.0] WAS Ø17.5 [1.69]; SEE SHEET 2 [CT59787]	SVP		
G	8-4-17	(D-6) DIM. Ø101.6 (4.00) ADDED [CT177004]	SRM		
H	9-27-18	ALL VIEWS AND DIMENSIONS UPDATED; SEE SHEET 2 [CT190707]	PAR		


APPROVALS	DATE
DRAWN MRS	11-5-09
CHECKED MRS	11-5-09
APPROVED ALC	11-5-09

TITLE	
DIMENSION PRINT	
SCALE 0.07	CAD NO.
DWG NO. ADV-7825	
SHEET 1 of 2	
D	



MODEL	ENCLOSURE WEIGHT KG [LBS]
STEEL WEATHER	310 [684]
STEEL SOUND	333 [734]
ALUMINUM SOUND	197 [434]

NOTE:
1. TANK (IF ORDERED) MOUNTS BELOW SKID
2. TANK MAY EXTEND BEYOND ENCLOSURE (DISCHARGE END ONLY)



EXHAUST OUTLET
SCALE 0.30

KOHLER CO.		METRIC	PRO-E
POWER SYSTEMS, KOHLER, WI 53044 U.S.A. THIS DRAWING IN DESIGN AND DETAIL IS KOHLER CO. PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH KOHLER CO. WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED.			
TITLE DIMENSION PRINT			
SCALE 0.07 CAD NO.		SHEET 2 of 2	
DWG NO. ADV-7825			D

REV	DATE	ON COMPOSITE DWGS. SEE PART NO. FOR REVISION LEVEL	BY	UNLESS OTHERWISE SPECIFIED - 1) DIMENSIONS ARE IN MILLIMETERS 2) TOLERANCES ARE:
E	2-5-13	SHEET 2 AND AQMD MODDED ADDED [CT32174]	SAM	X.XX ± 0.25 X.X ± 1.0 X ± 1.5
F	10-3-13	(A-5) Ø25.4 [1.0] WAS Ø17.5 [.69]; SEE SHEET 1 [CT59787]	SVP	ANGLES ± 0° 30' MAX.
G	8-4-17	SEE SHEET 1 [CT1770041]	SRM	THIRD ANGLE PROJECTION
H	9-27-18	ALL VIEWS AND DIMENSIONS UPDATED; SEE SHEET 1 [CT190707]	PAR	APPROVALS DRAWN SAM 2-5-13 CHECKED KEM 2-5-13 APPROVED KEM 2-5-13

125 MODEL 4S11, 4S13, 4R12X, 4R13X, 4T13X
150 MODEL 4S13, 4S15, 4R13X, 4T13X, 4S12X, 4S13X
RECONNECTABLE
IMPROVE MOTOR STARTING (IMS) RECONNECTABLE
600V & 1 PHASE ALTERNATORS
4045HF285 & 6068HF285 JOHN DEERE TIER III

CA AQMD READY ENCLOSURES
(NO SILENCER)