



MODEL	GENSET WEIGHT (WET) WITH ENCLOSURE		ENCLOSURE ONLY
	STEEL WEATHER	ALUMINUM SOUND	
40kW 4P5X/4Q5X	STEEL WEATHER	1010 Kg [2226 LBS]	239 Kg [527 LBS]
	STEEL SOUND	1015 Kg [2237 LBS]	244 Kg [538 LBS]
	ALUMINUM SOUND	922 Kg [2034 LBS]	152 Kg [335 LBS]
40kW 4P7BX/4Q7BX 45kW 4P7BX/4Q7BX 60kW 4P7BX	STEEL WEATHER	1046 Kg [2307 LBS]	239 Kg [527 LBS]
	STEEL SOUND	1051 Kg [2318 LBS]	244 Kg [538 LBS]
	ALUMINUM SOUND	959 Kg [2115 LBS]	152 Kg [335 LBS]
45kW 4P8X 50kW 4P8X/4Q8X 60kW 4P8X	STEEL WEATHER	1062 Kg [2341 LBS]	239 Kg [527 LBS]
	STEEL SOUND	1067 Kg [2352 LBS]	244 Kg [538 LBS]
	ALUMINUM SOUND	975 Kg [2149 LBS]	152 Kg [335 LBS]
45kW 4Q10X 50kW 4P10X/4Q10X 60kW 4P10X/4Q10X	STEEL WEATHER	1101 Kg [2427 LBS]	239 Kg [527 LBS]
	STEEL SOUND	1106 Kg [2438 LBS]	244 Kg [538 LBS]
	ALUMINUM SOUND	1014 Kg [2235 LBS]	152 Kg [335 LBS]

NOTE:
IF IBC CERTIFICATION IS REQUIRED, SEE SEISMIC
ADV FOR INSTALLATION INSTRUCTIONS

KG40-KG60
3PH RECONNECTABLE, 1PH
AND 600V ALTERNATORS

DIMENSIONS IN [] ARE INCH EQUIVALENTS

REV	DATE	ON COMPOSITE DWGS, SEE PART NO. FOR REVISION LEVEL	BY	DO NOT SCALE, REFERENCE THE MODEL FOR ALL UNSPECIFIED DIMENSIONS	
-	10-6-17	NEW DRAWING [CT179982]	JWL	UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS IN MILLIMETERS GENERAL TOLERANCES: N/A	
A	4-12-18	(D.2) 959 Kg [2115 LBS] WAS 1062 Kg [2341 LBS], 1062 Kg [2341 LBS] WAS 1067 Kg [2352 LBS], 1067 Kg [2352 LBS] WAS 1002 Kg [2209 LBS]	JWL		
		[PRO6949]	JWL	THIRD ANGLE PROJECTION	
		APPROVALS	DATE	KOHLER KOHLER, WISCONSIN 53044 THIS DRAWING IN DESIGN AND DETAIL IS KOHLER CO. PROPERTY AND MUST NOT BE USED EXCEPT IN CONNECTION WITH KOHLER CO. WORK. ALL RIGHTS OF DESIGN OR INVENTION ARE RESERVED. TITLE DIMENSION PRINT, 40-60 KW ENCLOSURE SCALE 0.40 CAD NO. SHEET 1 of 1 DWG NO. ADV-9039	
		DRAWN	JWL		10-6-17
		CHECKED	DJV		10-6-17
		APPROVED	KJT		10-6-17