




The KOHLER Advantage

- **Built to Last Since 1920**
For over 90 years, hospitals, airports and military bases around the world have depended on KOHLER generators.
- **Premium Warranty**
You get our premium 3-year limited warranty backed by a network of more than 10,000 dealers.
- **Custom Kits**
Legs, handles, wheels, lifting kits - whatever you want, any way you want it.
- **Free Loaner Program***
If your KOHLER generator ever goes down, just swing by one of our select dealers. We'll provide a free loaner unit for warranty repairs exceeding 24 hours.

Standard Features

- **Easy Refills**
Accu-Fill™ feature provides safe, easy refilling – and less spilling – with angled fuel inlet.
- **Extra Engine Protection**
Oil Sentry™ automatically shuts engine down in low-oil conditions.
- **OSHA-Ready**
When properly used, it's equipped to meet OSHA requirements.
- **Easy Reminders**
Maintenance Minder displays hours of run time and lights up to remind you of oil/spark plug/filter changes.
- **GFCI Outlets**
Ground-fault circuit interrupter detects unbalanced electrical current and safely shuts down power.
- **Safeguards Your Investment**
Automatic voltage regulator keeps voltage consistent to avoid surges or other damage.
- **Fuel Saver****
Auto-idle feature automatically set the engine to idle to save fuel.

Control Panel



* At participating dealers, based on availability.
** Featured only in model PRO5.2E

Specifications


Model Name	PRO5.2	PRO5.2E
Model spec	PA-PRO52-3002 PA-PRO52-2002 PA-PRO52-1001	PA-PRO52E-3002 PA-PRO52E-2002 PA-PRO52E-1001
Compliance	3002 (EPA/CARB) 2002 (EPA) 1001 (EPA/CSA)	
AC rated output (running watts)	4,500	
AC maximum output (motor starting watts)	5,200	
AC voltage	120/240	
AC frequency (Hz)	57.5-63	
Total Harmonic Distortion	≤ 5%	
Rated VAC amperage	37.5/18.75	
Max rated amperage	43.3/21.7	
Engine displacement	429cc	
Fuel type	Gasoline	
Engine RPM	3450-3750	
Recommended oil	SAE30	
Automatic voltage regulation	Yes	
Choke location	Manual on engine	
Fuel shut off	In tank w/filter	
Starting method	Recoil only	Recoil & Electric
Low oil shutdown method	Low level	
Neutral	Neutral Bonded to Frame	
Start switch type	Toggle Type Off-On (Red)	Toggle Type Off-On-Start (Red)
Switch location	On control panel	
Fuel gauge	Yes	
Fuel tank capacity	8 gal/30 liters	
Run time @ 50% (hours)	18	
Battery Type	Seal AGM	
Warranty - Residential	3 years	
Warranty - Commercial	3 years	

Available U-Spec™ Accessory System Options

- Wheel Kit (Ø10 by 3 inch)
- Leg Kit
- Wheelbarrow Handle Kit
- Auto-Locking Hand Truck Handle Kit
- Lifting Kit
- Extension Cord Management Kit
- Isolator Kit
- 12 Volt Battery Charger Cable
- Manual Transfer Switch

Generator Set Dimensions and Weights

A mm (in.):	747 (29.4)	Carton Length mm (in.):	777 (30.6)
B mm (in.):	544 (21.4)	Carton Width mm (in.):	572 (22.5)
C mm (in.):	566 (22.3)	Carton Height mm (in.):	599 (23.6)
D mm (in.):	1219 (48)	Shipping Weight lbs (kg)	
E mm (in.):	762 (30)	PRO5.2:	190 (86)
F mm (in.):	114 (4.5)	PRO5.2E:	214 (97)
G mm (in.):	140 (5.5)		
Unit Weight lbs (kg):			
PRO 5.2 :	180 (82)		
PRO 5.2E:	201 (91)		



NOTE: Dimensions are provided for reference only and should not be used for planning installation. Contact your local distributor for more detailed information.

Availability is subject to change without notice. The generator set manufacturer reserves the right to change the design or specifications without notice and without any obligation or liability whatsoever.

DISTRIBUTED BY:



© 2015 by Kohler Co. All rights reserved.