

**KOHLER**<sup>®</sup>**ISO 9001**  
KOHLER  
POWER SYSTEMS  
NATIONALLY REGISTERED

## The KOHLER Advantage

- **Built to Last Since 1920**  
For over 90 years, hospitals, airports and military bases around the world have depended on KOHLER generators.
- **Premium Warranty**  
You get our premium 3-year limited warranty backed by a network of more than 10,000 dealers.
- **Free Loaner Program\***  
If your KOHLER generator ever goes down, just swing by one of our select dealers. We'll provide a free loaner unit for warranty repairs exceeding 24 hours.

## Standard Features

- **Self-Priming**  
Automatically clears air out of the pump system and doesn't require water to start.
- **Protective Frame**  
A 360-degree roll cage design.
- **Pro-Grade Engine**  
Powered by a KOHLER Command PRO<sup>®</sup> engine, designed for professional-grade power.
- **Extra Engine Protection**  
Oil Sentry<sup>™</sup> automatically shuts engine down in low-oil conditions.
- **High-Power Engine Protection**  
Quad-Clean<sup>™</sup> air filtration and heavy-duty cyclonic air filter trap fine contaminants for maximum power and engine life.

## Available U-Spec<sup>™</sup> Accessory System Options

- Wheelbarrow handle kit
- Wheel kit
- Leg kit
- Cord management kit
- Isolator kit
- Hose kit


\* At participating dealers, based on availability.

## Specifications


Model Name	TP3.0
Pump Type	3 inch trash pump
Kohler Pump Spec	PA-TP30-3001
Compliance	3001 (CARB/EPA/CSA)
Engine cc	277
Oil-Sentry™ (Low oil protection)	Yes
Suction Diameter mm (in)	76.2 (3" NPT)
Suction Head Height m (ft)	8 (26)
Total Head Height m (ft)	26 (85)
Flow Rate L (gal per minute)	1300 (343)
Impeller	Cast Iron
Seals	Silicone Carbide
Max Pressure (PSI)	39
Priming Time	120 sec @ 16.4 ft
Fuel Type	Gasoline
Fuel Capacity L (gal)	7L (1.9gal)
Run Time (hours)	4.5
Warranty-Commercial/ Industrial Use	3 Years
Warranty-Consumer/ Recreational Use	3 Years

## Dimensions and Weights

A mm (in.):	686 (27)	Carton Length mm (in.):	701 (27.6)
B mm (in.):	531 (21)	Carton Width mm (in.):	546 (21.5)
C mm (in.):	541 (21.3)	Carton Height mm (in.):	579 (22.8)
D mm (in.):	140 (5)	Shipping Weight kg (lbs):	68 (151)
E mm (in.):	737 (29)		
Unit Weight kg (lbs):	62 (137)		



## Performance



NOTE: Dimensions are provided for reference only and should not be used for planning installation. Contact your local distributor for more detailed information.

Availability is subject to change without notice. The generator set manufacturer reserves the right to change the design or specifications without notice and without any obligation or liability whatsoever.

**DISTRIBUTED BY:**

© 2016 by Kohler Co. All rights reserved.