

**ISO 9001**  
**KOHLER**  
 NATIONALLY REGISTERED




### The KOHLER Advantage

- **Built to Last Since 1920**  
 For over 100 years, hospitals, airports and military bases around the world have depended on KOHLER generators.
- **Premium Warranty**  
 You get our premium 3-year limited warranty backed by a network of more than 10,000 dealers.
- **Custom Kits**  
 Legs, handles, wheels, lifting kits - whatever you want, any way you want it.
- **Free Loaner Program\***  
 If your KOHLER generator ever goes down, just swing by one of our select dealers. We'll provide a free loaner unit for warranty repairs exceeding 24 hours.

### Standard Features

- **Easy Refills**  
 Accu-Fill® feature provides safe, easy refilling - and less spilling - with angled fuel inlet.
- **Extra Engine Protection**  
 Oil Sentry™ automatically shuts engine down in low-oil conditions.
- **Easy Reminders**  
 Maintenance Minder™ displays hours of run time and lights up to remind you of oil/spark plug/filter changes.
- **GFCI Outlets**  
 Ground-fault circuit interrupter detects unbalanced electrical current and safely shuts down power.
- **Kohler DisCOVer™ CO Monitor**  
 Designed to limit carbon monoxide (CO) exposure.
- **Safeguards Your Investment**  
 Automatic voltage regulator (AVR) keeps voltage consistent to avoid surges or other damage.
- **Fuel Saver\*\***  
 Auto-idle feature automatically set the engine to idle to save fuel.

### Control Panel



\* At participating dealers, based on availability.

## Specifications


Model Name	PRO3.7
Model spec	PA-PRO37-1001 PA-PRO37-2001 PA-PRO37-2101† PA-PRO37-3001 PA-PRO37-3101†
Compliance	EPA/CARB (3001 & 3101 Specs only) EPA only (2001, 2101, & 1001 Specs only) CSA (All Specs)
AC rated output (running watts)	3,000
AC maximum output (motor starting watts)	3,700
AC voltage	120/240
AC frequency (Hz)	57.5-63
Total Harmonic Distortion	≤ 5%
Rated VAC amperage	25/12.5
Max rated amperage	30.8/15.4
Engine displacement	208cc
Fuel type	Gasoline
Engine RPM	3450-3750
Recommended oil	SAE30
Automatic voltage regulation	Yes
Choke location	Manual on Engine
Fuel shut off	In Tank with Filter
Starting method	Recoil Only
Low oil shutdown method	Low Level
Neutral	Neutral Bonded to Frame
Start switch type	Toggle Type Off-On (Red)
Switch location	On Control Panel
Fuel gauge	Yes
Fuel tank capacity	3.4 gal/ 13 liters
Run time @ 50% (hours)	9
Battery Type	Seal AGM
Battery Size	7.5 Apm hours
Warranty - Residential	3 Years
Warranty - Commercial	3 Years

## Available U-Spec® Accessory System Options

- Wheel Kit (Ø10 by 3 inch)
- Leg Kit
- Wheelbarrow Handle Kit
- Auto-Locking Hand Truck Handle Kit
- Lifting Kit
- Extension Cord Management Kit
- Isolator Kit
- 12 Volt Battery Charger Cable

## Generator Set Dimensions and Weights


A mm (in.):	615 (24.2)	Carton Length mm (in.):	630 (24.8)
B mm (in.):	488 (19.2)	Carton Width mm (in.):	498 (19.6)
C mm (in.):	487 (19.2)	Carton Height mm (in.):	523 (20.6)
D mm (in.):	1087 (42.8)	Shipping Weight lbs (kg):	
E mm (in.):	707 (27.8)	PRO3.7:	134 (61)
F mm (in.):	114 (4.5)		
G mm (in.):	140 (5.5)		
Unit Weight lbs (kg):			
PRO3.7:	126 (57)		



NOTE: Dimensions are provided for reference only and should not be used for planning installation. Contact your local distributor for more detailed information.

Availability is subject to change without notice. The generator set manufacturer reserves the right to change the design or specifications without notice and without any obligation or liability whatsoever.

## DISTRIBUTED BY:



† Models equipped with DisCOVer™ CO Monitor.