


# K-3536-C, K-4519-C K-4519-CR

## FEATURES

- 4" rough-in
- Vitreous china
- Elongated bowl
- Rear outlet
- Water-Guard® system
- Combination toilet
- Includes polished chrome trip lever
- Less seat and supply
- 3.5 gpf
- With Insuliner® insulated tank lining (-CU)
- With right-hand trip lever (K-4519-CR)
- With tank cover locks (-CT)



## CODES AND STANDARDS

- Conforms to ASME/ANSI A112.19.2M
- Conforms to ASME/ANSI A112.19.6M
- Conforms to The Energy Policy Act of 1992 (EPACT)
- IAPMO/UPC Listed
- Canadian Standards Association (CSA) Certified

## SPECIFIED MODEL

- K-3536-C, left-hand trip lever.
- K-4519-C, tank only .
- K-4519-CR, tank only with right-hand trip lever.

## COLORS


- 0 WHITE
- OTHER \_\_\_\_\_

### PRODUCT SPECIFICATION:

The elongated toilet combination shall be 4" rough-in with Kohler Water-Guard® system. Toilet shall be made of vitreous china. Toilet shall be 3.5 gpf. Toilet shall include polished chrome trip lever. Toilet shall be less seat and supply. Toilet shall have Insuliner® insulated tank lining (-CU). Toilet shall have right hand trip lever (K-4519-CR). Toilet shall have tank cover locks (-CT).

*We reserve the right to make revisions without notice in the design of fixtures or in packaging unless this right has specifically been waived at the time the order is accepted.*

## PRODUCT DIAGRAM



### Ordering Information

Applicable product with left-hand trip lever:		
Toilet	K-3536-C	shown
Tank	K-4519-C	not shown
Toilet with cover lock tank	K-3536-CT	not shown
Toilet with insuliner tank	K-3536-CU	not shown
Applicable product with right-hand trip lever:		
Tank	K-4519-CR	not shown
Tank with cover locks	K-4519-TR	not shown
Tank with insuliner	K-4519-UR	not shown
Accessories/hardware:		
Floor bolts (pr.)	21401	recommended
3/8" supply	K-7367	recommended
Seat	K-4652	recommended

### Product Information

Fixture:	
Configuration	2-piece, elongated
Gallons per flush	3.5 gallons
Passageway	2-1/4"
Water depth from rim	4-15/16"
Seat post hole centers	5-1/2"
Included Components:	
Bowl	K-4219-C
Tank	K-4519-C
Tank cover	80471
Bolt caps	52048
Trip lever	K-9404