


### Features

- 18-gauge stainless steel
- Under-mount
- Large single bowl
- Includes bottom bowl rack
- Includes installation hardware
- Use for standard 36" (914 mm) cabinet
- 35-1/2" (902 mm) x 21-1/4" (540 mm)

### UNDER-MOUNT APRON FRONT KITCHEN SINK K-3943



### Codes/Standards Applicable

Specified model meets or exceeds the following:

- ASME A112.19.3/CSA B45.4

### Colors/Finishes

- NA: None applicable

### Accessories

- CP: Polished Chrome
- ST: Stainless Steel
- Other: Refer to Price Book for additional colors/finishes

### Specified Model

Model	Description	Colors/Finishes
K-3943	Under-mount apron front kitchen sink	<input type="checkbox"/> NA
<b>Included Accessories</b>		
K-6474	Bottom bowl rack	<input type="checkbox"/> ST
<b>Optional Accessories</b>		
K-8801	Duostrainer® sink strainer	<input type="checkbox"/> CP <input type="checkbox"/> Other_____

### Product Specification

The under-mount apron front sink shall be made of 18-gauge stainless steel. Sink shall have large single basin. Sink shall include bottom bowl rack and installation hardware. Sink shall be 35-1/2" (902 mm) in length, 21-1/4" (540 mm) in width. Sink shall be used for standard 36" (914 mm) cabinet. Sink shall be Kohler Model K-3943-NA.

## Technical Information



Fixture*:	
Bowl area	32-1/2" (826 mm) x 17-3/16" (437 mm)
Water depth	9" (229 mm)
Drain hole	Ø 3-11/16" (94 mm)
* Approximate measurements for comparison only.	
Included components:	
Hardware kit (4 required)	91915
Cut-out template	1166719-7

## Installation Notes



Install this product according to the installation guide.

Allow a minimum of 3" (76 mm) clearance for the back 1" (25 mm) sink rim flange for clip attachment.

The 3/4" (19 mm) side rim flanges are supported without using the clip attachment. See the installation guide for further instructions.



*\*Allow clearance around the back sink rim for clip attachment.*



## Product Diagram