

Features

- Single-function rainhead
- MasterClean[™] sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Optimized sprayface for maximum performance
- 2.5 gpm (9.5 lpm) maximum flow rate

Material

Solid-brass construction for durability and reliability

Technology

 Katalyst[®] air-induction technology infuses water with air, creating bigger drops for a more powerful spray

Installation

1/2 -14 NPT connection

Recommended Products/Accessories

K-23723 Faucet cleaner



Codes/Standards

ASME A112.18.1/CSA B125.1 DOE - Energy Policy Act 1992 IAPMO Certification

KOHLER[®] Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.


Color Code Description





KOHLER, Faucets

Traditional 12" single-function rainhead, 2.5 gpm K-13694



Technical Information

All product dimensions are nominal.

Showerhead/Body Spray:

Rated maximum 2.5 gal/min (9.5 l/min) flow:

Notes

Install this product according to the installation instructions.

