

Features

- Articulating spout with 360° rotation offers superior clearance for filling pots on cooktops and ranges
- 22-3/4" (578 mm) swing spout reach
- 3.2 gpm (12.1 lpm) flow rate at 60 psi (4.14 bar)
- Single lever handle with main lever shutoff
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Deck-mount



Codes/Standards


ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
All applicable US Federal and State material regulations
IAPMO Certification


KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	VS	Vibrant® Stainless
	BL	Matte Black
	2MB	Vibrant® Brushed Moderne Brass



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 3.2 gal/min (12.1 l/min)

Pressure: 60 psi (4.1 bar)

Drain included: No

Spout:

Spout reach: 22-3/4" (578 mm)

Notes

Install this product according to the installation instructions.

Supply hose not included. Requires a flexible supply hose with a 3/8" compression nut and 1/2-14 NPSM nut.