Kingston™
Toilet tank, 1.28 gpf
K-25100

Features
- Ideal for commercial installations
- 1.28 gpf (4.8 lpf)
- Durable metal left-hand Polished Chrome trip lever
- Combines with a K-25076 or K-25076-SS bowl to create a complete K-25077 or K-25077-SS Kingston two-piece toilet
- Class Five® canister optimizes the flow out of the tank, harnessing gravity and the natural powerful reducing cascade of water to increase the power and effectiveness of the flush



Installation
- Three-bolt quick-connect installation
- Supply line sold separately

Recommended Products/Accessories
K-23726 Drain treatment

Codes/Standards
ASME A112.19.2/CSA B45.1
EPA WaterSense®
IAPMO Certification

KOHLER® Toilets and Seats Limited Warranty
See website for detailed warranty information.

Available Colors/Finishes
Color tiles intended for reference only.

Color	Code	Description
	0	White

KOHLER®

Kingston™

Toilet tank, 1.28 gpf

K-25100

No image available.
This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

Toilet type:	Bowl-mount
Waste Outlet:	Floor
Flush type:	Class Five

Notes

Install this product according to the installation instructions.

Install this product according to the installation instructions.