



**Evok™**

66" x 30" freestanding bath  
**K-25165**

### Features

- Freestanding design creates a striking focal point in your bathing area
- 17" (432 mm) depth offers a deep soaking experience
- Integral lumbar support
- Slotted overflow allows for deep soaking
- Center toe-tap drain color-matched to the bath

### Material

- Acrylic

### Installation

- Freestanding

### Recommended Products/Accessories

- K-23726 Drain treatment
- K-23732 Tub & shower cleaner






### Codes/Standards

- CSA B45.5/IAPMO Z124
- ASTM E162
- ASTM E662

### **KOHLER® Plastic Baths and Shower Bases Lifetime Limited Warranty**

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

Drain location:	Center
Basin area, bottom:	43" x 22-9/16" (1092 mm x 573 mm)
Basin area, top:	63-5/8" x 27-3/4" (1617 mm x 705 mm)
Weight:	138 lbs (62.6 kg)
Minimum floor load:	102 lbs/ft <sup>2</sup> (498 kg/m <sup>2</sup> )
Water depth:	17-1/16" (433 mm)
Water capacity:	78.7 gal (297.9 L)

## Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.