KOHLER®

Parohn®

One-light sconce

K-27858-SC01

Features

- Dramatic tapered fabric shades with metal trim and decorative sphere motif create a beautiful accent for interior spaces
- Modernist references are reinterpreted to create a timeless design that works in a range of interior styles and settings
- This collection is at home in modern and traditional interiors
- A great piece for almost any space — master bathroom, guest bathroom, hallway, or bedside
- Candelabra base (E12) socket, works best with clear or frosted LED candelabra type B bulbs (sold separately)
- Suitable for damp locations, per UL 1598

Material

- Manufactured with quality materials and complemented with a meticulous finishing process
- Durable finishes engineered to last and designed to coordinate with KOHLER faucet finishes



Codes/Standards

UL 1598
CSA C22.2 No. 250.0

KOHLER® Indoor Lighting Fixtures Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.


Color	Code	Description
	SNL	Polished Nickel
	CPL	Polished Chrome
	GNL	Gunmetal
	2GL	Brushed Moderne Brass
	2PL	Polished Brass


KOHLER®

Parohn®

One-light sconce

K-27858-SC01





Required Electrical Service

One dedicated circuit required.

Lights:	120 V, 0.5 A, 60 Hz

Technical Information

All product dimensions are nominal.

Material:	Steel
Number of Lights:	1
Lighting Type:	Socket-based
Socket Type:	E-12 Candelabra
Number of Shades:	1
Shade Type:	Fabric
Hanging Type:	Non-hanging
Electrical component rating:	Socket Rating: 60 Hz, 60 W