

27-1/2" undermount single-bowl kitchen sink K-28000

#### Features

- 30" (762 mm) minimum base cabinet width
- Single bowl
- 9-1/2" (241 mm) depth provides generous workspace
- Includes K-80038 bottom sink rack
- Includes cutout templates and installation clips
- Matte finish offers rich, dimensional color

#### Material

- KOHLER Neoroc<sup>®</sup> composite is durable and built to withstand day-to-day cleaning tasks
- Solid color throughout the sink
- Heat-resistant up to 750°F
- Scratch-, stain-, chip-, and thermal-shock-resistant

# Installation

- Undermount
- Easy to install in a one-person, single-day project

#### **Recommended Products/Accessories**

K-8801 Sink drain and strainer with tailpiece K-8799 Sink drain and strainer basket K-23726 Drain treatment K-23730 Neoroc® cleaner

#### **Optional Products/Accessories**

K-11352 Disposal Flange with Stopper K-9000 P-Trap

### **Included Components**

K-80038 Sink Rack



# **Codes/Standards**

CSA B45.5/IAPMO Z124 IAPMO Certification

### KOHLER<sup>®</sup> Neoroc<sup>®</sup> Sinks Lifetime Limited Warranty

See website for detailed warranty information.

# **Available Colors/Finishes**


Color tiles intended for reference only.

Color	Code	Description
	CM6	Matte White
	CM7	Matte Graphite
	CM1	Matte Black
	CM2	Matte Brown
	СМЗ	Matte Taupe
	CM4	Matte Grey





# Cairn® 27-1/2" undermount single-bowl kitchen sink K-28000



# **Technical Information**

All product dimensions are nominal.			
Min. base cabinet width:	30" (762 mm)		
Bowl area (Only):	Length: 25-9/16" (649 mm) Width: 16-3/8" (416 mm) Bowl depth: 9-1/2" (241 mm) Water depth: 9-1/2" (241 mm)		
Template:	Under-mount, 1311528, required, included		

# Notes

Install this product according to the installation instructions.

Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1-800-43-FOCUS). Kohler Co. is not responsible for cut-out errors when the incorrect cut-out template is used.

