

Features

- Full coverage spray produces an encompassing spray ideal for everyday use
- Best-in-class audio with sound by Harman Kardon®
- Easily toggle between two sound-performance settings, "Shower" and "Normal," depending upon where speaker is being used
- IPX7-rated waterproof speaker
- Magnetic showerhead holds speaker securely in place, yet removes easily for charging
- Featuring BLUETOOTH wireless technology, allowing you to pair any compatible device to stream your favorite music, podcast, or other audio content
- Wireless speaker can be used outside the shower space, independent of the showerhead, to stream music in any room
- Speaker provides up to nine hours of play time
- Charging dock quickly and easily charges speaker
- Download the KOHLER Konnect® app for additional functionality
- 1.75 gpm (6.6 lpm) maximum flow rate at 80 psi (5.5 bar)

Material

- Durable material construction
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Wall-mount
- Shower arm and flange sold separately

Recommended Products/Accessories

K-7395 Shower Arm and Flange



Codes/Standards

ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
IAPMO Certification

KOHLER® One-Year Limited Warranty KOHLER® Faucet Lifetime Limited Warranty




See website for detailed warranty information.

The BLUETOOTH® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Kohler Co. is under license. Other trademarks and trade names are those of their respective owners.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BN	Vibrant® Brushed Nickel
	BL	Matte Black



Technical Information

All product dimensions are nominal.

Power source:	Battery - DC, included
Amplifier channels:	1 at 10 W per channel
Charge time:	3 hours
Usage time:	9 hours
Bluetooth® range:	32.8 ft (10 m)
Bluetooth® version:	5.0
Max. Ambient temp:	140°F (60°C)

Showerhead/Body Spray:

Rated maximum flow:	1.75 gal/min (6.6 l/min)
Pressure:	80 psi (5.5 bar)

Notes

Install this product according to the installation instructions.

Follow local building electrical codes.

A Bluetooth® wireless device is required to stream music.

For use with automatic compensating valves rated at 1.50 gal/min (5.7 L./min) or less.