



**Vault™**  
Top-/Under-Mount Kitchen Sink  
**K-3823-3**

**Features**

- 36-inch minimum base cabinet width.
- Large/medium bowls.
- 9" depth provides generous workspace.
- Three faucet holes.
- Includes installation hardware and bottom sink rack.
- SilentShield® sound-absorption technology offers quieter performance.

**Material**

- Handcrafted from 18-gauge stainless steel.
- Premium 18-gauge stainless steel.

**Installation**

- Top-mount or undermount.

**Recommended Products/Accessories**

K-6646 Left-Bowl Sink Rack  
K-6647 Right-Bowl Sink Rack  
K-8801 Sink Strainer  
K-8799 Sink Strainer  
K-23726 Drain treatment  
K-23729 Stainless steel cleaner

**Optional Products/Accessories**

K-6429 Utility Rack  
K-6432 Saddle Towel Bar  
K-6434 Saddle Utility Rack  
K-6667 Wood Cutting Board  
1177161 Installation Clip Kit  
K-11352 Disposal Flange with Stopper

**Included Components**

Product consists of:

K-6646 Left-Bowl Sink Rack  
1130570 Hardware Kit, Self-Rimming




**Codes/Standards**

ASME A112.19.3/CSA B45.4

**Lifetime Limited Warranty for  
KOHLER® Stainless Steel Sinks**

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

|                          |                                                                                                             |
|--------------------------|-------------------------------------------------------------------------------------------------------------|
| Bowl configuration:      | Off-set Large/small                                                                                         |
| Installation:            | Top-mount, Under-mount                                                                                      |
| Min. base cabinet width: | 36" (914 mm)                                                                                                |
| Bowl area:               | Length: 17-1/2" (445 mm)<br>Width: 16-9/16" (421 mm)<br>Bowl depth: 9" (229 mm)<br>Water depth: 9" (229 mm) |
| Bowl area:               | Length: 11-5/8" (295 mm)<br>Width: 16-9/16" (421 mm)<br>Bowl depth: 9" (229 mm)<br>Water depth: 9" (229 mm) |
| Drain hole:              | 3-7/8" (98 mm)                                                                                              |
| Template:                | 1130823-7, required, included                                                                               |

### Notes

Install this product according to the installation instructions.

Allow 3/4" (19 mm) clearance beyond the back of the bowl for the wood cutting board (optional accessory).