

Features

- Elongated bowl offers added room and comfort
- Skirted trapway simplifies cleaning
- Revolution 360® flushing technology generates a forceful swirling motion to keep the bowl clean longer
- Comfort Height® feature offers chair-height seating that makes sitting down and standing up easier for most adults
- Patented ReadyLock® installation system, a simple solution for skirted toilets, saves time, hassle, and eliminates the need to drill into the floor for standard 12" (305 mm) rough-in
- CleanCoat™ surface treatment inhibits the growth of water scale and mineral stains for improved ease of cleaning
- Combines with the K-4143, K-4143-RA, or K-5711 tank to create a complete K-3814, K-3814-RA, or K-5709 Corbelle toilet
- Patented ReadyLock® installation system, a simple solution for skirted toilets, saves time, hassle, and eliminates the need to drill into the floor for standard 12" (305 mm) rough-in

Installation

- Standard 12" (305 mm) rough-in
- 10" and 14" (254 mm and 356 mm) rough-in kits also available
- Seat sold separately

Recommended Products/Accessories

K-4143 Toilet tank, 1.28 gpf
K-23726 Drain treatment



Codes/Standards






ASME A112.19.2/CSA B45.1
IAPMO Certification

KOHLER® Toilets and Seats Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|---|------|--------------|
|  | 0 | White |
|  | 96 | Biscuit |
|  | NY | Dune |
|  | 95 | Ice™ Grey |
|  | 7 | Black Black™ |

No image available.

This product is a component and not intended to be a standalone installation.

Technical Information

All product dimensions are nominal.

| | |
|------------------|----------------|
| Toilet type: | Floor-mount |
| Flush type: | Revolution 360 |
| Trap passageway: | 2-1/8" (54 mm) |
| Rough-in: | 12" (305 mm) |

Notes

Install this product according to the installation instructions.