

Features

- Optimized sprayface creates a denser uniform spray pattern for consistent coverage and feeling of warmth
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- 2.0 gpm (7.6 lpm) maximum flow rate
- 1/2" NPT connection
- Requires K-7392, K-7394, or K-7396 shower arm (sold separately)

Material

- Solid-brass construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Technology

- Katalyst® air-induction technology infuses water with air, creating bigger drops for a more powerful spray

Installation

- Ceiling-mount

Recommended Products/Accessories

K-23723 Faucet cleaner

Optional Products/Accessories

K-7396 3" ceiling-mount single-function rainhead arm & flange
K-7392 12" ceiling-mount single-function rainhead arm & flange
K-7394 6" ceiling-mount single-function rainhead arm & flange
K-10124 Right-angle Shower Arm and Flange




Codes/Standards

ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Showerhead/Body Spray:

Rated maximum flow: 2 gal/min (7.6 l/min)

Notes

Install this product according to the installation guide.

NOTICE: To ensure your valve will provide safety at the lowest flow rates, choose an automatic compensating valve with the appropriate minimum flow rating. For a showerhead rated at 2.0 gal/min (7.6 l/min) maximum, use with an automatic compensating valve rated at 1.6 gal/min (6.1 l/min) or less.