

## Features

- Three preinstalled tank bolts save installation time
- 1.28 gpf high-efficiency toilets provide significant water savings of up to 16,500 gallons per year versus an old 3.5-gallon toilet without sacrificing performance
- Qualifies as an HET(High-Efficiency Toilet). Consumer rebates are available in some municipalities
- Left-hand Polished Chrome trip lever
- KOHLER's canister flush valve harnesses the natural force of gravity and optimizes flushing performance
- Class Five® canister optimizes the flow out of the tank, harnessing gravity and the natural powerful reducing cascade of water to increase the power and effectiveness of the flush



## Installation

- 14" (356 mm) rough-in

## Recommended Products/Accessories

- K-4199 Elongated toilet bowl
- K-23726 Drain treatment



## Codes/Standards




ASME A112.19.2/CSA B45.1  
EPA WaterSense®  
IAPMO Certification

## KOHLER® Toilets and Seats Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	0	White
	96	Biscuit
	7	Black Black™

No image available.  
This product is a component and not intended to be a standalone installation.

## Technical Information

All product dimensions are nominal.

Toilet type: Bowl-mount  
Flush type: Class Five  
Rough-in: 14" (356 mm)

## Notes

Install this product according to the installation instructions.