Fluence®

Frameless Sliding Shower Door

K-702219-L



Features

- Frameless, 1/4" (6 mm) thick Crystal Clear tempered glass.
- Gently curved inside and outside towel bars complete the look of this door.

Technology

- Continuous door panel guide mechanism for smooth, quiet sliding action.
- CleanCoat® nanotechnology provides a smooth, nonstick surface to help prevent buildup of water stains, bacteria and mildew on your glass, to make it easy to clean and keep it looking like new.
- Out-of-plumb adjustability for simpler installation.

Installation

- Not for use in hospitality.

Recommended Products/Accessories

K-23723 Faucet cleaner

Included Components

Additional Components:

Hardware kit

Codes/Standards

CPSC 16CFR 1201

ANSI Z97.1

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	SHP	Bright Polished Silver


Available Glass Options

Code	Description
L	Crystal Clear

Fluence®

Frameless Sliding Shower Door

K-702219-L



Technical Information

All product dimensions are nominal.

Installation type:	For shower base installation
Opening style:	Sliding/Bypass
Opening Width - Min:	37" (940 mm)
Opening Width - Max:	40" (1016 mm)
Walk-through - Min:	14-7/8" (378 mm)
Walk-through - Max:	17-7/8" (454 mm)
Base-To-Wall Radius – Max:	1/2" (13 mm)
Glass thickness:	1/4" (6 mm)
Glass coating:	CleanCoat®

Notes

Install this product according to the installation guide.

The vertical opening should be a minimum of 77-3/4" (1975 mm) to allow for installation clearance.