

Features

- Two-handle gooseneck bathroom sink faucet
- 3-11/16" (94 mm) gooseneck spout with rosespray
- 7-5/16" (186 mm) wall-to-spout outlet
- 1.2 gpm (4.5 lpm) maximum flow rate
- Lever handles with red/blue indexing (ADA-compliant with correct installation)
- Optional decorative handle covers
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Less drain
- Adjustable flanges
- External NPT connections
- Complies with the Safe Drinking Water Act (SDWA)

Material

- Brass

Installation

- 3" vertical wall-mount installation
- Pairs with the Brockway wall-mounted wash sink

Recommended Products/Accessories

- K-3200 36" wall-mount utility sink
- K-3202 48" wall-mount utility sink
- K-3203 60" wall-mount utility sink
- K-23723 Faucet cleaner



ADA	CSA B651	OBC
------------	-----------------	------------

Codes/Standards



ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
All applicable US Federal and State material regulations
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
ADA
ICC/ANSI A117.1
CSA B651
OBC
IAPMO Certification


KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	SR	Vibrant Bright Nickel



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 1.2 gal/min (4.5 l/min)

Pressure: 60 psi (4.1 bar)

Drain included: No

Spout:

Spout reach: 3-11/16" (93 mm)

Notes

Install this product according to the installation instructions.

ADA compliant for handles only.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.