



Karing®

One-piece elongated smart toilet, 1.08 gpf
K-77780

Features

- Compact, streamlined one-piece smart toilet with integrated personal cleansing
- Elongated bowl offers added room and comfort
- 1.08 gallons per flush (gpf)
- Advanced bidet functionality with self-cleaning wand and precision air dryer
- Adjustable settings for heated seat, dryer and water temperature
- Motion-activated, hands-free opening/closing of cover
- LED lighting illuminates the bowl to serve as a nightlight
- Stainless steel wand offers adjustable spray shape, position, water pressure, temperature, pulsate, and oscillate functions
- Bowl is automatically misted prior to use for more effective rinsing while flushing
- English-language touch-screen LCD remote control
- Self-cleaning function uses UV light and electrolyzed water systems to automatically clean the wand surfaces
- Automatic deodorizer fan reduces odors
- Power Lite® flushing technology offers a powerful, water-efficient 1.08-gallon flush
- Automatic flushing after every use; flush can also be controlled by the touch-screen remote or backup button
- Minimum static pressure of 20 psi required

Installation

- Standard 12" (305 mm) rough-in

Recommended Products/Accessories

K-23726 Drain treatment



Codes/Standards

ASME A112.19.2/CSA B45.1
ASME A112.4.2/CSA B45.16
DOE - Energy Policy Act 1992
EPA WaterSense®
California Energy Commission (CEC)
UL 1951
CSA C22.2 No. 14
CSA C22.2 No. 68
IAPMO Certification
cUL Listed
UL Listed

KOHLER® Intelligent Toilet and C3® Cleansing Seat Three-Year Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------



0	White
---	-------

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.


For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

6-17-2024 22:24 - US

THE BOLD LOOK
OF **KOHLER®**



Karing®
One-piece elongated smart toilet, 1.08 gpf
K-77780



Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

120 V, 15 A, 60 Hz

Technical Information

All product dimensions are nominal.

Toilet type: Floor-mount

Waste Outlet: Floor

Bowl shape: Elongated

Flush type: Pressure Lite

Trap passageway: 2-7/8" (73 mm)

Water surface size: 12" x 9-1/2" (305 mm x 241 mm)

Rim to water 4-7/8" (124 mm)

surface:

Rough-in: 12" (305 mm)

Seat-mounting 5-1/2" (140 mm)

holes:

Fixture Supply Requirements

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

6-17-2024 22:24 - US

Notes

Install this product according to the installation instructions.

This product is designed for installation with the electrical and water supplies located through either the wall or the floor.

If the rough-in distance is less than 12" (305mm) the seat may strike the wall when it is opened. Confirm the rough-in is 12" (305 mm) before installing the toilet.

THE BOLD LOOK
OF **KOHLER**