



60" x 32" drop-in bath **K-850** 

#### **Features**

- 60"L x 32"W x 18-1/4"H
- The only two-person bath that fits into a standard 5' alcove
- Spacious design accommodates up to two bathers
- Safeguard® slip-resistant surface provides excellent traction underfoot

#### Material

KOHLER® enameled cast iron

## Installation

- Drop-in, undermount, or alcove
- Requires cable pop-up bath drain and bath drain trim (sold separately)

## **Required Products/Accessories**

K-23857 Bath drain trim

or

K-78440 33" cable pop-up bath drain

## **Recommended Products/Accessories**

K-586 Under-Mount Installation Kit

K-1172 Adjustable feet

K-1179 Vinyl Tiling-in Bead

K-1491 Bath/Whirlpool Pillow

K-1601 Bath/whirlpool footstop, removable

K-706000-D3 Frameless Sliding Bath Door

K-706000-L 62" H sliding bath door with 1/4"-thick glass

K-706004-D3 Frameless Sliding Bath Door

K-706004-L Frameless Sliding Bath Door

K-23726 Drain treatment

K-23725 Cast iron cleaner

K-31796 Above-the-floor bath drain kit

K-31798 Bath drain kit



# ADA

## Codes/Standards

ASME A112.19.1/CSA B45.2 ASTM F462 ADA ICC/ANSI A117.1 IAPMO Certification

## **KOHLER® Enameled Cast Iron Bath** and Shower Base Lifetime Limited Warranty

See website for detailed warranty information.

#### **Available Colors/Finishes**

Color tiles intended for reference only.


| Color | Code | Description   |
|-------|------|---------------|
|       | 0    | White         |
|       | 96   | Biscuit       |
|       | NY   | Dune          |
|       | 95   | Ice™ Grey     |
|       | 58   | Thunder™ Grey |
|       | 7    | Black Black™  |






**KOHLER**®


60" x 32" drop-in bath **K-850** 



No change in measurements if connected with drain illustrated. (K-23856-NA)







#### **Technical Information**

All product dimensions are nominal.

Drain location: Reversible

Basin area, bottom: 40-1/2" x 20" (1029 mm x 508 mm)
Basin area, top: 52-3/4" x 24" (1340 mm x 610 mm)

Weight: 250 lbs (113.4 kg)

Minimum floor load: 58 lbs/ft² (283.2 kg/m²)

Water depth: 13-5/8" (346 mm)

Water capacity: 60 gal (227.1 L)

Cutout: Drop-in, 58-1/2" x 30-1/2" (1486 mm x

775 mm)

Template: Under-mount, K-586, required, not

included

Minimum flat for 3" (77 mm)

door:

### **Notes**

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Kit is required for under-mount installations (sold separately).

ADA compliant when installed to the specific

requirements of these regulations.

