KOHLER®

Medicine Cabinet
K-CB-CLR1620FS

Features
- Recessed installation only
- Two adjustable tempered-glass shelves offer additional bathroom storage
- Full-overlay mirrored door with beveled edges
- Mirrored interior
- 108° opening capability for easy cabinet access



Material
- Anodized aluminum construction with a durable rustproof and chip-resistant finish
- Anodized aluminum construction with a durable rustproof and chip-resistant finish

Installation
- Can be installed with left- or right-hand swing


Recommended Products/Accessories
K-10570 One-light sconce
K-10571 Two-light sconce
K-11365 One-light sconce
K-11366 Two-light sconce
K-23723 Faucet cleaner

Codes/Standards
None Applicable

KOHLER® One-Year Limited Warranty
See website for detailed warranty information.

KOHLER®

Medicine Cabinet
K-CB-CLR1620FS



Technical Information
All product dimensions are nominal.

Notes
Install this product according to the installation guide.

When determining the height of the medicine cabinet, ensure the mirrored door will clear all obstacles (such as a faucet). A minimum distance of 3" (76 mm) is required.

For surface-mount, use anchors (not provided) rated for the loaded weight of this product.

This cabinet is designed for either right or left door swing. Check for obstructions.