



Prologue®

33" top-/undermount single-bowl kitchen sink kit

K-R31466-1PC

Features

- 36" (914 mm) minimum base cabinet width
- Single bowl
- 9" (229 mm) depth provides generous workspace
- Rounded 0.98" (25 mm) corners are easy to clean
- Single faucet hole
- SilentShield® sound-absorption technology offers quieter performance
- Two-function pull-down sprayhead allows you to switch from aerated stream to Sweep® spray
- Sweep® spray features specially angled nozzles that form a wide, powerful blade of water to sweep your dishes and sink clean
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Box includes: Sink, assembled Vibrant Stainless pull-down faucet, sink rack, drain and strainer, installation hardware

Material

- Premium 18-gauge stainless steel
- Durable material construction
- KOHLER stainless steel sinks resist corrosion and tarnishing

Installation

- Top-mount or undermount

Recommended Products/Accessories

- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

Optional Products/Accessories

- K-11352 Disposal Flange with Stopper

Included Components

- 1419715-VS Vibrant Stainless pull-down kitchen faucet
- K-31473 Sink rack
- 7400 Stainless Steel Sink Drain and Strainer



Codes/Standards

ASME A112.18.1/CSA B125.1
ASME A112.19.3/CSA B45.4
NSF/ANSI/CAN 61
NSF/ANSI/CAN 372
All applicable US Federal and State material regulations
DOE - Energy Policy Act 1992
California Energy Commission (CEC)
IAPMO Certification

KOHLER® Stainless Steel Sinks
Lifetime Limited Warranty
KOHLER®
Faucet Lifetime Limited Warranty
See website for detailed warranty information.

